

HEMIFES - Electrical stimulator for strengthening of weak muscles

TECHNICAL DATA		
operating mode	Alternating (6s/6s) intermittent trains of stimulating pulses, or external manual switch control	
pulses	biphasic charge balanced current stimulating pulses	
amplitude	mA	0 – 50
frequency	Hz	25
pulse width	ms	0,25
power consumption	mA	30 (max)
size	mm	120 x 65 x 30
weight (including batteries)	g	140
power source	2 x 1,5 V IEC LR6 (alkaline cell) 2 x 1,2 V IEC HR6 (NiMH rechargeable cell)	